Shut off and just float.



Our PROTOLON Shore Connection cables will keep the ships sustainably energised.









Our PROTOLON Shore Connection cables will keep the ships sustainably energised.

As you sit at the dock of the bay, watching the tide roll away, our PROTOLON SC cable will work hard to keep the vessels energised from the electrical grid while berthing. Instead of keeping the diesel engines running, the vessels get more sustainable energy while saving on fuel and reducing the carbon footprints. A win-win for everyone. Just lay back and breathe easily.

PROTOLON SC

Application

PROTOLON SC is the perfect choice for MV and LV connection systems to supply the ship with electrical power. The MV version also includes fibre optics for easy access to telecom networks. As PROTOLON SC is feeding the vessels with electricity and digital data, the diesel engines can be turned off to save on fuel and pollution. The cable is also suitable for permanent immersion in water.

MAIN FEATURES

- Compliant to international standard IEC/ISO/IEEE 80005
- Designed for reeling application and also suitable on semi-fixed systems
- Flexible and mechanically robust for high reliability
- Resistant to UV, ozone and moisture. Can be permanently immersed in water.
- Suitable for container ships, cruise vessels, RoRo and RoPax vessels
- Oelivered with pre-mounted plugs or terminations on request

COMMITTED TO SUSTAINABILITY

Sustainable grids are key to reduce carbon footprints.

The future development and integration of renewable energy sources will be key for our planet's sustainability. But there is more to it. Other aspects need to be considered to make a grid truly environmentally friendly. That is why our products are designed and created in compliance with international industry standards with the goal of improving environmental performance, cutting the use of harmful substances, reducing pollution and improving recyclability.

PROTOLON(SC) (N)TSKWOEU 0.6/1 kV

Low voltage cable for Shore Connection systems.



PROTOLON(SC) (N)TSKWOEU 0.6/1 kV									
Global data									
Brand	PROTOLON(SC)								
Type designation	(N)TSKWOEU								
Standard	Based on DIN VDE 0250-813 based on IEC/ISO/IEEE 80005-3								
Construction characteristics									
Conductor	Bare copper, class 5								
PE-Conductor	Bare copper, class 5								
Insulation	Basic material EPR, type 3GI3, acc. to DIN VDE 0207 Part 20								
Core identification	Natural coloured insulation with black numbering for power and control cores, earth conductors coloured in green-yellow								
Inner sheath	Vulcanized rubber compound, basic material EPR								
Inner sheath colour	Natural								
Outer sheath	Abrasion and tear-proof high grade rubber compound								
Outer sheath colour	Black								
Electrical parameters									
Rated voltage	0.6/1 kV (600/1000V)								
Max. permissible operating voltage AC	0.7/1.2 kV								
Max. permissible operating voltage DC	0.9/1.8 kV								
Current carrying capacity	Acc. to DIN VDE 0298, Part 4								

PROTOLON(SC) (N)TSKWOEU 0.6/1 kV								
Chemical parameters								
Flame propagation	DIN EN 60332-1-2							
Resistance to oil	Acc. to DIN EN 60811-404 and DIN VDE 0473-811-404, paragraph 10							
Weather resistance	Unrestricted use outdoors and indoors, resistant to ozone, UV and moisture. Water resistant.							
Thermal parameters								
Max. operating temperature of the conductor	90°C							
Max. short circuit temperature of the conductor	250°C							
Ambient temperature for fixed installation	Min -40 °C ; max +80 °C							
Ambient temperature in fully flexible operation	Min -25 °C ; max +80 °C							
Mechanical parameters								
Max. tensile load on the conductor	20 N/mm²							
Max. tensile load on the conductor during acceleration	25 N/mm²							
Bending radii min.	Acc. to DIN VDE 0298 part 3							
Additional tests	Based on IEC/ISO/IEEE 80005-3							

PROTOLON(SC) (N)TSKWOEU 0.6/1kV											
Number of	nber of Part diameter radiu s x cross number max. min. max. m				Bending radius free	Weight	Permissi- ble tensile	Dynamic tensile	Conductor resistance	Current carrying	Short circuit
cores x cross section		moving min. mm	min. kg/km	force max. N	force max. N	at 20 °C max. Ω/km	capacity (1) A	current (conductor) kA			
3x185+2x95/2+ 1x(4x2,5)	20258591	18.6	63.9	67.9	340	9500	11100	13875	0.106	461	26.46

Special designs available upon request.

PROTOLON(SC) (N)TSCGEWOEU 6/10 kV

Medium voltage cable for Shore Connection systems.



PROTOLON(SC) (N)TSCGEWOEU 6/10 kV								
Global data								
Brand	PROTOLON(SC)							
Type designation	(N)TSCGEWOEU							
Standard	Based on DIN VDE 0250-813 based on IEC/ISO/IEEE 80005-1							
Construction characteristics								
Conductor	Bare copper, class 5							
PE-Conductor	Bare copper, class 5							
Insulation	Basic material EPR, type 3GI3, acc. to DIN VDE 0207 Part 20							
Core identification	Natural coloured insulation with black semiconductive layer							
Optical fiber	Multi-mode G62.5							
Core arrangement	Three core design laid around a central support element							
Support element	Aramid yarns and rubber covering							
Inner sheath	Vulcanized rubber							
Outer sheath	Abrasion and tear-proof high grade rubber compound							
Outer sheath colour	Bright red/red							
Electrical parameters								
Rated voltage	6/10 kV							
Max. permissible operating voltage AC	6.9/12 kV							
Max. permissible operating voltage DC	9/18 kV							
Current carrying capacity	Acc. to DIN VDE 0298, Part 4							

DDOTOLON/SS/ANX	SCCEMOEN C/10 lay								
PROTOLON(SC) (N)TSCGEWOEU 6/10 kV									
Chemical parameters									
Flame propagation	DIN EN 60332-1-2								
Resistance to oil	Acc. to DIN EN 60811-404 and DIN VDE 0473-811-404, paragraph 10								
Weather resistance	Unrestricted use outdoors and indoors, resistant to ozone, UV and moisture. Water resistant.								
Thermal parameters									
Max. operating temperature of the conductor	90°C								
Max. short circuit temperature of the conductor	250°C								
Ambient temperature for fixed installation	Min -40 °C ; max +80 °C								
Ambient temperature in fully flexible operation	Min -25 °C ; max +80 °C								
Mechanical parameters									
Max. tensile load on the conductor	20 N/mm²								
Max. tensile load on the conductor during acceleration	25 N/mm²								
Bending radii min.	Acc. to DIN VDE 0298 part 3								
Additional tests	Acc. to IEC/ISO/IEEE 80005-1								

PROTOLON(SC) (N)TSCGEWOEU 6/10kV												
Number of	Part	Conduc- tor	Earth conduc- tor	Outer diameter		free moving p	Weight (ap- prox.) kg/km Permissi- ble tensile force max. N	ble tensile		Conductor resistance at 20 °C	Current carrying capacity	Short circuit current
section	section max. ma	diameter max. mm	min. mm	max. mm	max. N			max. Ω/km	(1) A	(conductor) kA		
3x185+1x95+ 1x(5x2,5ST +4x3G62,5LWL)C	20129011	17.8	13	74	78	780	10850	11100	13875	0.106	461	26.46

Special designs available upon request.

(1) Nominal current carrying capacity for rubber cables laid on a surface, at 30 °C ambient temperature (see also VDE 0298-4, Table 15).

Please check our homepage: www.prysmiangroup.de for more details.



The planet's pathways

PRYSMIAN

Prysmian Kabel und Systeme GmbH Phone: +49 (0) 30 3675 40 kontakt@prysmiangroup.com

© All rights reserved by Prysmian 2024-01 | Version 3.

Technical data, dimensions and weights are subject to change. All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.









