


**UNPARALLELED PERFORMANCE,
UNMATCHED RELIABILITY.**

SPREADERFLEX XTRM: The Ultimate Cable Solution for Your Mobile Harbour Crane.

SPREADERFLEX XTRM is our high-performance spreader cable specifically designed for the demanding requirements of mobile harbour cranes, making it the ideal choice for applications that demand both power and durability.



**Our answer
to your most
demanding
vertical reeling
requirements.**



KEY FEATURES

- Cross-section: 37x2.5+CAN
BUS 1x(2x0.24mm²)
- Voltage class: 0.6/1kV
- Tensile strength: >4.5kN
- Breaking strength: >20kN
- Speed: max. 160m/min
- Max. lifting height: 90m (with
a total cable length of 130m)
- Weight: 1.5kg/m
- Diameter: 28.7 +/-1.0mm

**Further design options
upon request**

Please contact us for further information:

Jana Blechschmidt

Head of Global Cranes

M +49(0) 163 3675 223

jana.blechschmidt@prysmian.com

Ghina Ayudiya Putri

Key Account OEM Specialties

M +49 173 4688177

ghinaayudiya.putri@prysmian.com